

Axicon 6515 Barcode Verifier



Mid Range Barcode Verifier

Product Summary

Independently tested & certified to meet international standards, the Axicon 6515 has been specifically designed to read all linear barcodes with a width of up to 125mm (4.9") including quiet zones. Our development program means that not only will your verifier always meet the latest ISO/ANSI standard, but also a wide range of application standards including GS1-128 & ISBN/ISSN. A wide range of additional reporting tools is also provided.

Typical Application

The Axicon 6515 is capable of verifing linear barcodes up to 125mm (4.9") wide

making it ideal for both point of sale and traded unit barcodes typically those printed on thermal/thermal transfer printers. For this reason it is widely regarded as the industry standard across many business sectors.

Installation

Simply install the software on your computer, plug in the verifier and you can be confident that your barcodes are being checked to the highest standards.





- ISO/ANSI Verification Standards
- Static Scan Reflectance Measurement
- Al Data Content Checker (for GS1-128 & GS1 DataBar etc.)
- Multi Language user Interface
- USB Connectivity



Church Road
Weston on the Green,
Oxfordshire,
OX25 3QP, U.K.
Tel +44 (0)1869 351 155
email: sales@axicon.com
www.axicon.com



Axicon 6515 Barcode Verifier



Software Specifications

Symbologies Verified: GS1 SYMBOLOGIES: EAN-8, EAN-13 (with or without addons), ITF-14/Case Code, GS1-DataBar (all symbologies),

GS1-128, UPC-A, UPC-E (with or without addons).

OTHER SYMBOLOGIES: Code 39, Code 93, Code 128, Codabar, ITF, MSI Plessey, Pharmacode (Laetus: optional extra).

Application Standards: AIAG, Belgian Pharmacode (MSI), Belgian Pharmacode (Unique), CIP39, Coupon Codes (UK, USA, Euro), Code Vignette,

GS1 AI Check, HIBC, ISBN/ISSN, Italian Pharmacode (IMH), LPPR, M&S, PZN, SISAC, Variable Measure Codes (Branded,

Instore, Australian).

Analysis Performed on Relevant

Logging:

Symbologies: Full ISO/ANSI Parameter Analysis (Rmin, Rmax, Global Threshold, Symbol Contrast, Min Edge Contrast, Modulation,

Defects, Decodability, Decode), Decodability per Symbol Character, Average Bar Gain, Check Digit Validation, Data Length, Nominal Bar Width Analysis (X Dimension), Print Contrast Measurement (PCS), Symbol Structure

including Parity, Subsets & Start/Stop Characters, Quiet Zone Validation, Wide to Narrow Ratio Display and Validation.

Diagnostics Windows: Parameter Detail Results, Dimensional Analysis, Pass/Fail, Scan Reflectance Profile, Static Scan Reflectance, Summary,

Traditional Results, Application Identifier Data Content Checker (for GS1-128, GS1-DataBar), Product-Look-Up. Scan Saving and Loading - stores complete details of scan file data. Allows for remote diagnostics and also for

increased traceability.

Calibration Logging: A record of date and time to show when the hardware has been calibrated is kept - vital for ISO 9000 records.

Configurable Options: Audible Warnings, Calibration Expiry Warning, Changeable Pass / Fail and Warning Colours, Optional Check Digit

Validation (Code 39, Codabar, ITF), File Saving, Multi-Scan Averaging, Pass Grade, Print Options, Window Sizes and

ositions.

Error Messages: Check Digit Error, Data Content Error, Incorrect Wide to Narrow Ratio, Print Quality Failure, Product Look-Up Error,

Quiet Zone Error, Reference Decode Algorithm Error, Structure Error, X Dimension Range Checking.

Plugins Available: Code 39 full ASCII, CSV File Saving, Gen Spec, Job Reference, Product Look-up, Text Look-up, Time Zone, UPC, User

Data, User Name, (see also Application Standards).

Additional Software: Pharmacode (Laetus) - Decode and Analysis of Laetus Pharmacode.

ScanDB - Reporting Tool transferring data from saved scans into a .csv file.

RepGen - Configurable report generation tool.

HARDWARE SPECIFICATIONS

Dimensions: 145 x 113 x 128mm (5.7" x 4.4" x 5"), Scan Width - 125mm / 4.9 inches including quiet zones

Weight: 675 gms (23.8oz)

Construction: Cast Aluminium and ABS plastic

Interface: USB

Power Consumption: Current draw 150mA - supplied from USB host. Nominal Measuring: 5mil, 6mil, 10mil, 20mil.

Aperture: The software automatically identifies the symbology/nominal bar size (X dimension) and adjusts the aperture size

in order to comply with the symbology specifications and International Standards.

Wavelength of Light: 660 nanometers

GENERAL INFORMATION

Print of Analysis: A printed report can be produced on any connected printer. The report will be automatically resized to suit the

output media. Printouts can be produced for the main verification information (including: Decoded Number, Time & Date, Number of Scans, Code Type, Average ISO/ANSI Grade, Average Bar Gain, Magnification, Check Character, Quiet Zone & Individual Parameters) Scan Reflectance Profiles, Dimensional Analysis, also for GS1-128 & GS1-DataBar

Data Content information and Plugin Results.

GS1 Verification Template supported. Customised reports available via RepGen and ScanDB utilities.

Standard Accessories: Transit Case, Calibration Sheet, Start-up Guide, Software CD, Compliance Certificates.

System Requirements: PC running Windows 95 (SP2) or later, Mac OSX 10.2 or later.

Environmental: Operating Temperature: 10° to 40°C

Storage Temperature: -20° to 70°C

Relative Humidity: 25% to 80% @ 40°C non-condensing

Warranty: 2 year parts and labour - return to bench.

All trademarks are acknowledged as belonging to their respective companies.

Due to Axicon's continuing product improvement programs, specifications and features herein are subject to change without notice.

Please note that not all features are available on Mac OS

THE BARCODE EXPERTS

Church Road, Weston on the Green, Oxfordshire, OX25 3QP, U.K. Tel +44 (0)1869 351 155 email: sales@axicon.com

www.axicon.com